

EmergencyToilet.com

info@emergencytoilet.com



Decontamination Building Safety Shower or Eye Wash Station

- Internal Dimensions: 48" x 48" x 95"
- Multiple Skylights
- Paddle Handled Door Handles
- Recycled Plastic Floor
- External and Internal Lock
- No Maintenance
- Can be Either Portable or Permanent
- Immediate Water Run-Off
- Heavy Duty
- Electrical Service Option
- Optional Stand Alone Shower System
- Optional Pressure Operated Water System



These onsite Decontamination Buildings are designed with flexibility in mind which will allow modification to meet most any specification. Regulation compliance need not be a budget breaker. With our decontamination shelters, cost can be controlled. This unit is made with 100% non-adsorbent materials.

Multiple Person Fast Access Decontamination Building

- Internal Dimensions: 60" x 84" x 42"
- Translucent Roof
- Recycled Plastic Floor
- Open Immediate Access
- No Maintenance
- Can be Either Portable or Permanent
- Immediate Water Run-Off
- Heavy Duty
- Electrical Service Option
- Optional Stand Alone Shower System
- Optional Pressure Operated Water System
- Can Be Made With 100%
Non-Adsorbent Materials**



EmergencyToilet.com

Eyewash Station

Eye Wash Station
½ " or 1" Walls

Options

Paddle Handled Door Knob
Electricity
Safety Light
Key Lock Off Hours
Unrestricted Access



Eye Wash Station
½" Walls

1 Eye Wash Station
1" Walls

Electric or Gravity Flow Portable Eye Wash Station
1" Model 4848EHD Shown



Model 4848HD
Inside View



Drain or Vinyl
Flooring



Signage Included

Used in conjunction with our patented Comfort Station #6721967. Decontamination Shelter can be used in any application either behind – incorporated inside – or on either the left or right side of the Comfort Station.

Safety and Hygiene Station is designed to work in conjunction with our patented Comfort Station (#6721967). This system is designed to meet or exceed health and safety job site regulations.

Pump system will be constantly tested with the hourly use of the attached Comfort Station fixtures.

Water Pressure Pump System



Ground Level



First Aid Supplies

Eliminates the Need for Portable Toilets

Bolt-on Capabilities

Can Be Combined with a Cooling Structure or Trailer.

Pump plumbing can be directed to drain the decontamination shelter waste water holding tank.



Drinking Fountain Waste Water Drains Into Waste Tank or on The Ground



Door (entrance cover) Is Removed During Working Hours and Replaced with Plastic Strips

Issued and Pending Patents